



PC-3TE SERIES

2-14 μm IR PHOTOCONDUCTORS THERMOELECTRICALLY COOLED



FEATURES

- High performance in the 2-14 μm range
- Fast response
- Convenient to use
- Wide dynamic range
- Compact, rugged and reliable
- Low cost
- Prompt delivery
- Custom design upon request

DESCRIPTION

PC-3TE- λ_{opt} photodetectors series (λ_{opt} - optimal wavelength in micrometers) feature IR photoconductive detector on three-stage thermoelectrical cooler. The devices are optimized for the maximum performance at λ_{opt} . Cut-on wavelength is limited by GaAs transmittance (~0.9 μm). Bias is needed to operate photocurrent. Performance at low frequencies (<20 kHz) is reduced due to 1/f noise. Highest performance and stability are achieved by application of variable gap (HgCd)Te semiconductor, optimized doping and sophisticated surface processing. Custom devices with quadrant cells, multielement arrays, different windows, lenses and optical filters are available upon request.

Standard detectors are available in TO-8 packages with BaF₂ windows. Other packages, windows and connectors are also available.

SPECIFICATION

@20°C

CHARACTERISTICS	UNITS	PC-3TE-9	PC-3TE-10.6	PC-3TE-12	PC-3TE-13
λ_{opt}	μm	9	10,6	12	13
Detectivity ¹⁾ : @ λ_{peak} , 20kHz	cmHz ^{1/2} /W	≥2.9×10 ⁹	≥4.5×10 ⁸	≥1.8×10 ⁸	≥1.2×10 ⁸
@ λ_{opt} , 20kHz		≥1.5×10 ⁹	≥2.5×10 ⁸	≥9×10 ⁷	≥6×10 ⁷
Responsivity-Width product @ λ_{opt} 1×1mm	Vmm/W	≥15	≥3	≥1.5	≥1
Time Constant	ns	<7	<5	<5	<4
1/f Corner Frequency	kHz	1 to 20	1 to 20	1 to 20	1 to 20
Bias current-Width Ratio	mA/mm	4 to 10	4 to 10	4 to 10	4 to 10
Sheet Resistance	Ω/sqr	60 to 200	40 to 150	40 to 150	40 to 150
Operating Temperature	K	~210			
Acceptance angle, F/#	deg, -	70, 0.87			

¹⁾ Data sheet states minimum guaranteed D* values for each detector model. Higher performance detectors can be provided upon request.

Type	Length [mm]									
	0.025	0.05	0.1	0.2	0.25	0.5	1	2	3	4
PC-3TE-9	X	X	X	X	X	X	X	X		
PC-3TE-10.6	X	X	X	X	X	X	X	X		
PC-3TE-12	X	X	X	X	X	X	X	X		
PC-3TE-13	X	X	X	X	X	X	X	X		

X – standard detectors



129/133 Poznanska St., 05-850 Ozarow Mazowiecki, Poland; tel. +48 22 733 54 20; fax +48 22 733 54 26; e-mail: info@vigo.com.pl

Please note: the information contained in this document is subject to change without further notification. VIGO System reserves the right to alter the performance and any resulting specifications.VS-11-05-18MB