


2.17 PVM series

2.17.1 2.0 – 13.0 μm HgCdTe ambient temperature photovoltaic multiple junction detectors

PVM series features uncooled IR photovoltaic multiple junction detectors based on sophisticated HgCdTe heterostructures for the best performance and stability. The detectors are optimized for the maximum performance at λ_{opt} . They are especially useful as large active area detectors operating within 2 to 13 μm spectral range.

Spectral response ($T_a = 20^\circ\text{C}$)



Exemplary spectral detectivity, the spectral response of delivered devices may differ.


Specification ($T_a = 20^\circ\text{C}$)

Parameter	Detector type			
	PVM-8	PVM-10.6		
Active element material	epitaxial HgCdTe heterostructure			
Optimum wavelength λ_{opt} , μm	8.0	10.6		
Detectivity $D^*(\lambda_{\text{peak}})$, cm·Hz ^{1/2} /W	$\geq 1.2 \times 10^8$	$\geq 2.0 \times 10^7$		
Detectivity $D^*(\lambda_{\text{opt}})$, cm·Hz ^{1/2} /W	$\geq 6.0 \times 10^7$	$\geq 1.0 \times 10^7$		
Current responsivity-active area length product $R_i(\lambda_{\text{opt}})L$, A·mm/W	≥ 0.008	≥ 0.002		
Time constant τ , ns	≤ 4	≤ 1.5		
Resistance R , Ω	50 to 300	20 to 150		
Active area A, mm×mm	$1 \times 1, 2 \times 2, 3 \times 3, 4 \times 4$			
Package	TO39	BNC	TO39	BNC
Acceptance angle Φ	$\sim 90^\circ$	$\sim 102^\circ$ *, $\sim 124^\circ$ **	$\sim 90^\circ$	$\sim 102^\circ$ *, $\sim 124^\circ$ **
Window	none			

* Aperture C = Ø4 mm.


** Aperture C = Ø6 mm

Mechanical layout, mm




Parameter	Value	
Active area, mmxmm	1×1, 2×2	3×3, 4×4
C, mm	Ø4	Ø6
Acceptance angle Φ	~102°	~124°

C - aperture



Function	Pin number
Detector	1, 2
Chassis ground	3



Dedicated preamplifier



small SIP-TO39